

Genspec®

DYTHIC
GD4200-USB
USB PRESSURE TRANSDUCER

ESITECHTO ON A SECTION OF SECTION



- Silicon-on-Sapphire pressure sensor technology
- Choice of pressure ranges from vacuum to 5,000 bar
- Accuracy (NLHR) ±0.15% of span BFSL
- Auto detect and configuration
- USB 2.0 compatible
- ESI-USB© downloadable software with auto update
- Measure & record up to 16 pressure inputs together
- Create customised test certificate
- Automatic temperature compensation
- Support for easy integration with applications created by C#, VB, Labview and Excel VBA (api dll library)
- 2m lead & carry case included



ECHNOLOGY L

GD4200-USB : -1.0 to 2.5 bard t: Serial USB





Description

The GD4200-USB© Digital Pressure Transducer has been designed to measure, analyse and record pressure directly on your computer without the need for costly I/O interface boards. It allows the user to measure up to 16 pressure inputs simultaneously and easily create customised test certificates.

The transducer is powered by the computer's USB port, data is then presented on the PC via the ESI-USB© configurable Windows Interface software. It has instant connection with auto-detection, and will configure automatically with your desktop, laptop or Windows tablet via USB protocol. The sample rate enables dynamic pressures to be measured with up to 21 bit resolution at user selectable speeds up to 1,000 Hz. For real-time analysis, data transferred to the PC is achieved without loss of accuracy or bandwidth. This pressure transducer is USB 2.0 compatible, the ESI-USB© interface configuration and analysis software is compatible exclusively with Windows© 7 (32bit & 64bit), 8, 8.1 and 10. Data can be displayed in graphical or tabular form, with a choice of pressure units and fully adjustable scales. Data can be saved to a file or exported to Excel/ PDF.

The unique Silicon-on-Sapphire sensor technology provides outstanding performance and gives excellent stability over a wide temperature range. Excellent measurement accuracy provides high resolution with a precision greater than 1 in 10,000. Nine pressure ranges have been carefully selected to enable the user to cover any pressure that the application requires, from vacuum up to 5,000 bar, via the use of the ESI-USB© digitally self scaling software.

Each unit requires free download of the ESI-USB® software and is supplied with 2m USB lead, rated to IP68, and a convenient carry case.

ESI-USB© software



Graph Screen



Monitor Screen

Dimensions (in mm)



1/4" BSPM (G1/4) OR 1/4" NPTM OR F250-C



Technical Data

Type:	GD4200-USB			
Sensor Technology:	Silicon-on-Sapphire (SoS)			
Output signal:	USB 2.0 compatible			
Supply Voltage:	5 VDC via USB bus			
Pressure Reference:	Gauge (default); Absolute reference input by user			
Standard Pressure Ranges:	-1 to 2.5 bar; 0 -16 bar; 0-100 bar; 0-400 bar; 0-1,000 bar; 0-1,500 bar; 0-2,000 bar; 0-4,000 bar, 0-5,000 bar			
Standard Pressure Ranges (other):	User selectable for psi and other measurement units			
Overpressure Safety:	2x up to 400 bar; 1.5x for 1,000 bar; 1.1x for 1,500 bar; 1.5x for 2,000 bar; 1.25x for 4,000 bar; 1.2x for 5,000 bar			
Accuracy NLHR:	≤ ±0.15 % of span BFSL			
Sample Rate:	User selectable to 1,000 samples per second (1,000 Hz) Resolution: 21 bits for ≤5 Hz; 16 bits for >5 - 1,000 Hz			
Operating Ambient Temperature:	-20 °C to +85 °C (-4 °F to +185 °F)			
Operating Media Temperature:	-50 °C to +125 °C (-58 °F to +257 °F)			
Storage Temperature:	+5 °C to +40 °C (+41 °F to +104°F) Recommended Best Practice			
Temperature Effects:	±1.5 %FS total error band for -10 °C to +80 °C. Typical thermal zero and span coefficients ±0.015 %FS/ °C			
Electromagnetic Compatibility:	EN61326-1, EN61326-2-3 (Laboratory equipment)			
Wetted Parts:	Titanium alloy			
Pressure Media:	All fluids compatible with titanium alloy			
Pressure Connection:	1/4" BSP male (G1/4); 1/4" NPT male or F250-C (Autoclave)			
Electrical Connection:	Mating to USB mini B socket for cable connection to PC. Supplied with 2m USB lead rated to IP68 as standard			
Software compatibility:	Windows 7, Windows 8, Windows 8.1 and Windows 10			



Order Matrix

Output	Туре	Electrical Connector	Pressure Range	Process Connection	
USB 2.0 full speed connection	GD4200-USB				
Electrical Connection / Option					
Mating to USB mini B socket					
Pressure Range in bar					
-1 to 2.5 bar	02.5				
0-16 bar	0016				
0-100 bar	0100				
0-400 bar	0400				
0-1,000 bar	1000				
0-1,500 bar	1500				
0-2,000 bar	2000				
0-4,000 bar	4000				
0-5,000 bar	5000				
Process Connection					
1/4" BSP male (G1/4)					
1/4" NPT male					
Autoclave F-250-C female (for pressures above 1500bar)					

Order Number Example GD4200-USB1500AB

For options not listed please contact sales team.

DISCLAIMER: ESI Technology Ltd operates a policy of continuous product development. We reserve the right to change specification without prior notice. All products manufactured by ESI Technology Ltd are calibrated using precision calibration equipment with traceability to international standards.



- **t.** +44(0)1978 262 255
- e. sales@esi-tec.com